



VE312H

vector,IP65,36M,UV-stabil,DC/AC,with knockouts

### Technical properties

#### Connection

Number of conduit inlets 12

#### Voltage

Nominal voltage 400 - 400 V

#### Installation, mounting

Suitable for outdoor usage Yes

Mounting on Surface mounting

#### Electric current

Rated current 63 A

#### Equipment

Number of rails 3

Number of rows 3

Number of section in width 1

With lock No

Has mounting plate No

#### Capacity

Number of modules 36

#### Functions

With conduit inlets Yes

#### Dimensions

Height 552 mm

Width 310 mm

Depth 151 mm

Number of width units 36

#### Cover, door

Number of cabinet doors 1

Number of locks 0

Door/cover is transparent Yes

#### Materials

Material Plastic

RAL code 7035

Colour Light grey

Ultraviolet-resistant

Yes

**Safety**

---

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65
Locking type	Snap on lock, Without lock
Glow wire test	850 °C