



VF104TT



Small distributor,golf,flush,1row,4M,IP40,MS-terminal,AUS,N+PE,transparent door

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	225 mm
Installation height	189 mm
Width of installed product	204 mm
Width in division units	4
Built-in height	189 mm
Built-in width	170 mm

Cover, door

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	850 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------