



VF112PTQ

Small distributor,golf,flush,1row,12M,IP40,QC-terminal,N+PE,white door

Technical properties

Configuration

Number of modules	12
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	293 mm
Installation height	257 mm
Width of installed product	352 mm
Width in division units	12
Built-in width	318 mm

Cover, door

Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
Material	plastic

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of rails	1
Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test

850 °C

Safety

IK protection code against mechanical impacts

07

Protection class

isol.class II

REACH conform

No

RoHS conform

Yes

Halogen free

No

Impact strength

IK07