



VF118TT



**Small distributor,golf,flush,1row,18M,IP40,MS-terminal,ANZ,N+PE,transparent door**

## Technical properties

### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

### Electric current

Rated current	80 A
---------------	------

### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

### Capacity

Number of modules	18
-------------------	----

### Functions

With conduit inlets	Yes
---------------------	-----

### Dimensions

Height	293 mm
Width	460 mm
Depth	97,50 mm
Built-in height	257 mm
Built-in width	426 mm
Built-in depth	72 mm
Number of width units	18

### Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	Yes

### Materials

Material	Plastic
----------	---------

RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

#### **Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	850 °C