



VF418PT



Small distributor,golf,flush,4row,IP40,72M,MS-terminal,Australia,N+PE,white door

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	72
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	688 mm
Installation height	652 mm
Width of installed product	460 mm
Width in division units	18
Built-in height	652 mm
Built-in width	426 mm

Cover, door

Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	4
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	4
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	0
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	Yes
---------------------	-----

Safety

Protection index IP	IP40
---------------------	------

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------