



VS112PT



Small distributor,golf,surface,1row,IP40,12M,MS-terminal,ANZ,N+PE,white door

Technical properties

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	80 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	12
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	252 mm
Width	282 mm
Depth	99 mm
Number of width units	12

Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	No

Materials

Material	Plastic
RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

Subject to technical modifications

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	650 °C