



VS212PTQ

Small distributor,golf,surface,2row,IP40,24M,QC-terminal,N+PE,white door

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Configuration

Number of modules	24
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	377 mm
Width of installed product	282 mm
Width in division units	12

Cover, door

Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Equipment

Number of rows	2
Quantity of rails	2
Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
--------------------	--------

Safety

Subject to technical modifications

IK protection code against mechanical impacts	07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
Halogen free	No
Impact strength	IK07