



VS218PT



**Small distributor,golf,surface,2row,IP40,36M,MS-terminal,AUS,N+PE,white door**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 36

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 80 A

**Dimensions**

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 377 mm

Width of installed product 390 mm

Width in division units 18

**Cover, door**

Type of door closing Latch

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use No

Subject to technical modifications

**Settings**

---

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

---

Number of rows	2
Quantity of section in width	1
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

**Standards**

---

GWT Glow wire test	650 °C
European directive WEEE	concerned

**Safety**

---

IK protection code against mechanical impacts	07
Protection class	isol.class II
Impact strength	IK07

**Use conditions**

---

Operating temperature	-25...40 °C
-----------------------	-------------