



VS218TT



**Small distributor,golf,surface,2row,IP40,36M,MS-terminal,AUS,N+PE,transpare door**

## Technical properties

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Configuration

Number of modules	36
-------------------	----

### Electric current

Rated current	63 A
---------------	------

### Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	377 mm
Width of installed product	390 mm
Width in division units	18

### Cover, door

Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	Door
Transparent cover or door	Yes

### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

### Equipment

Number of rows	2
Quantity of rails	2
Can be accessorized	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

### Standards

GWT Glow wire test	650 °C
--------------------	--------

### Safety

Subject to technical modifications

IK protection code against mechanical impacts	07
Protection index IP	IP40
Protection class	isol.class II
Impact strength	IK07