



VS318PZD

Small distributor,golf,surface,MM,54M,3row,white door,slotted

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	54
-------------------	----

Dimensions

Depth of wall niche	72 mm
Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	500 mm
Width of installed product	390 mm
Width in division units	18
Thickness of sidewall material	3 mm

Cover, door

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of units	18
Number of rows	3

Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	IK07
REACH conform	No
RoHS conform	Yes
Halogen free	No