



VS418PT



**Small distributor,golf,surface,4row,IP40,72M,MS-terminal,AUS,N+PE,white door**

#### Technical properties

##### Architecture

Fixing mode	surface-mounting
-------------	------------------

##### Functions

With a pipe-in lead	Yes
---------------------	-----

##### Configuration

Number of modules	72
-------------------	----

##### Main electrical features

Nominal voltage	400 V
-----------------	-------

##### Electric current

Rated current	80 A
---------------	------

##### Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	647 mm
Width of installed product	390 mm
Width in division units	18

##### Cover, door

Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

##### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

##### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	4
Quantity of section in width	1
Quantity of rails	4
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------