



VT12F

12M 1Row DIN Flush Metal BOX, No Door

Technical properties

Connection

Number of conduit inlets	16
--------------------------	----

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Has mounting plate	No
--------------------	----

Capacity

Number of modules	12
-------------------	----

Dimensions

Height	304 mm
--------	--------

Width	354 mm
-------	--------

Depth	10 mm
-------	-------

Built-in width	304 mm
----------------	--------

Built-in depth	60 mm
----------------	-------

Number of width units	12
-----------------------	----

Cover, door

Number of locks	0
-----------------	---

Door/cover is transparent	No
---------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------