



## 12M1Row DIN Surface Metal BOX,10.5M Door

### Technical properties

#### Connection

|                          |    |
|--------------------------|----|
| Number of conduit inlets | 16 |
|--------------------------|----|

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 230 - 415 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

#### Equipment

|                    |    |
|--------------------|----|
| Number of rails    | 1  |
| Number of rows     | 1  |
| Has mounting plate | No |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 12 |
|-------------------|----|

#### Dimensions

|                       |        |
|-----------------------|--------|
| Height                | 259 mm |
| Width                 | 309 mm |
| Depth                 | 71 mm  |
| Built-in depth        | 70 mm  |
| Number of width units | 12     |

#### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Number of locks           | 0  |
| Door/cover is transparent | No |

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9002       |
| Colour   | Grey white |

#### Safety

|                      |                   |
|----------------------|-------------------|
| Protection class     | Isolation class I |
| Impact resistance IK | IK05              |

