



VT24S

## 24M 2Row DIN Surface Metal BOX, No Door

### Technical properties

#### Connection

Number of conduit inlets	16
--------------------------	----

#### Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

#### Equipment

Number of rails	2
-----------------	---

Number of rows	2
----------------	---

Has mounting plate	No
--------------------	----

#### Capacity

Number of modules	24
-------------------	----

#### Dimensions

Height	419 mm
--------	--------

Width	369 mm
-------	--------

Depth	71 mm
-------	-------

Built-in depth	70 mm
----------------	-------

Number of width units	12
-----------------------	----

#### Cover, door

Number of locks	0
-----------------	---

Door/cover is transparent	No
---------------------------	----

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

#### Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------