



VT36S

### 36M 3Row DIN Surface Metal BOX, No Door

#### Technical properties

##### Connection

Number of conduit inlets	16
--------------------------	----

##### Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Equipment

Number of rails	3
Number of rows	3
Has mounting plate	No

##### Capacity

Number of modules	36
-------------------	----

##### Dimensions

Height	609 mm
Width	369 mm
Depth	71 mm
Built-in depth	70 mm
Number of width units	12

##### Cover, door

Number of locks	0
Door/cover is transparent	No

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Materials

Material	Steel
RAL code	9002
Colour	Grey white

##### Safety

Protection class	Isolation class I
Impact resistance IK	IK05