



VT48S

48M 4Row DIN Surface Metal BOX, No Door

Technical properties

Connection

Number of conduit inlets	16
--------------------------	----

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

Equipment

Number of rails	4
-----------------	---

Number of rows	4
----------------	---

Has mounting plate	No
--------------------	----

Capacity

Number of modules	48
-------------------	----

Dimensions

Height	750 mm
--------	--------

Width	465 mm
-------	--------

Depth	71 mm
-------	-------

Built-in depth	70 mm
----------------	-------

Number of width units	16
-----------------------	----

Cover, door

Number of locks	0
-----------------	---

Door/cover is transparent	No
---------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------