



VZ091

## Spare door,vector,IP65 for VE103

### Technical properties

#### Architecture

Intended door position	left
Fixing mode	Clamping

#### Dimensions

Depth of installed product	13.5 mm
Internal depth	13.5 mm
Height of installed product	115 mm
Width of installed product	82 mm
Built-in height	115 mm
Built-in width	82 mm

#### Cover, door

Material thickness cover	2.2 mm
Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	Yes

#### Materials

Colour	stone grey
Colour	transparent
Material	plastic
Type of surface treatment	untreated

#### Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

#### Equipment

Number of rows	1
Quantity of section in width	1
Number of keys	1

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	Yes

Subject to technical modifications

RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-25...40 °C