



VZ098

**Spare door,vector,IP65 for VE312**

**Technical properties**

**Architecture**

Intended door position	left
Fixing mode	Clamping

**Dimensions**

Depth of installed product	17 mm
Internal depth	17 mm
Height of installed product	398 mm
Width of installed product	280 mm
Built-in height	398 mm
Built-in width	280 mm

**Cover, door**

Material thickness cover	2.9 mm
Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	Yes

**Materials**

Colour	stone grey
Colour	transparent
Material	plastic
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	Yes
--------------------------	-----

**Equipment**

Number of rows	3
Quantity of section in width	1
Number of keys	1

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
--------------	-----

**Use conditions**

---

Operating temperature	-25...40 °C
-----------------------	-------------