



VZ607N

Door,golf,white,accessory,for VF/VS118

Technical properties

Architecture

Intended door position left

Dimensions

Depth of installed product 16.5 mm

Internal depth 16.5 mm

Height of installed product 250 mm

Width of installed product 388 mm

Built-in height 250 mm

Built-in width 388 mm

Cover, door

Number of keylock of the door 0

Door leave single

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Surface appearance glossy

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use No

Equipment

Number of rows 1

Quantity of section in width 1

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature

-25...40 °C