



VZ624N

**Door,golf,transparent,accessory,for VF/VS212**

**Technical properties**

**Architecture**

|                        |          |
|------------------------|----------|
| Intended door position | left     |
| Fixing mode            | Clamping |

**Dimensions**

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 16.5 mm |
| Internal depth              | 16.5 mm |
| Height of installed product | 375 mm  |
| Width of installed product  | 280 mm  |
| Built-in height             | 375 mm  |
| Built-in width              | 280 mm  |

**Cover, door**

|                                   |           |
|-----------------------------------|-----------|
| Type of door closing              | Latch     |
| Number of keylock of the door     | 0         |
| Door type for switch gear cabinet | Stop door |
| Door leave                        | single    |
| Transparent cover or door         | Yes       |

**Materials**

|                           |             |
|---------------------------|-------------|
| Colour                    | transparent |
| Colour                    | transparent |
| Material                  | plastic     |
| Type of surface treatment | untreated   |

**Installation, mounting**

|                          |    |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

**Equipment**

|                              |   |
|------------------------------|---|
| Number of rows               | 2 |
| Quantity of section in width | 1 |

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|   |               |
|---|---------------|
| IK protection code against mechanical impacts | IK07          |
| Protection index IP                           | IP40          |
| Protection class                              | isol.class II |

**Use conditions**

---

Operating temperature

-25...40 °C