



VZ630N

Door,golf,transparent,accessory,for VF/VS418

Technical properties

Architecture

Intended door position	left
Fixing mode	Clamping

Dimensions

Depth of installed product	16.5 mm
Internal depth	16.5 mm
Height of installed product	645 mm
Width of installed product	388 mm
Built-in height	645 mm
Built-in width	388 mm

Cover, door

Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	Yes

Materials

Colour	transparent
Colour	transparent
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	4
Quantity of section in width	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes

Halogen free

Yes

Use conditions

Operating temperature

-25...40 °C