



VZ856N

Door,golf,white,slotted,VDI,accessory,for VF/VS219

Technical properties

Architecture

Intended door position	left
Fixing mode	Clamping

Dimensions

Depth of installed product	16.5 mm
Internal depth	16.5 mm
Height of installed product	500 mm
Width of installed product	388 mm
Built-in height	500 mm
Built-in width	388 mm

Cover, door

Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	3
Quantity of section in width	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP40
Protection class	isol.class II

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------