



WBHP120-MB

### Allure Single GPO 20A Matt Black

#### Technical properties

##### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Main electrical features

|           |       |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

##### Dimensions

|        |        |
|--------|--------|
| Height | 77 mm  |
| Width  | 117 mm |

##### Installation, mounting

|                   |                        |
|-------------------|------------------------|
| Entries           | cable entries bevelled |
| Mounting type     | flush-mounted          |
| Installation mode | for screw fastening    |

##### Connection

|                    |                      |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

##### Scope of delivery

|                   |  |
|-------------------|--|
| Scope of delivery | supplied with standard tapered point 32 mm fixing screws |
|-------------------|--|

##### Equipment

|                                     |   |
|-------------------------------------|---|
| Number of socket outlets switchable | 1 |
|-------------------------------------|---|

##### Safety

|              |     |
|--------------|-----|
| RoHS conform | Yes |
| Halogen free | No  |

##### Identification

|                  |        |
|------------------|--------|
| Main design line | Allure |
|------------------|--------|