



WBHP1S

Allure Single GPO 10A

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Materials

Colour	white
Surface appearance	glossy

Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
--------------------	----------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	1
With transparent product label holder	No

Safety

IK protection code against mechanical impacts	IK08
REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection

Identification

Main design line	Allure
------------------	--------