



WBHP1S-MW

Allure Single GPO 10A MW

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V AC |
| Frequency | 50 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Installation, mounting

| | |
|-------------------|------------------------|
| Entries | cable entries bevelled |
| Mounting type | flush-mounted |
| Installation mode | for screw fastening |

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

Scope of delivery

| | |
|-------------------|--|
| Scope of delivery | supplied with standard tapered point 32 mm fixing screws |
|-------------------|--|

Equipment

| | |
|-------------------------------------|---|
| Number of socket outlets switchable | 1 |
|-------------------------------------|---|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|------------------|--------|
| Main design line | Allure |
|------------------|--------|