



WBHP2S



Allure Double GPO

Technical properties

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

Dimensions

Built-in depth flush-mounted boxes	18 mm
------------------------------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC), Thermoplastic

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate

Protection	Without enhanced contact protection
Related Series	allure