



WBHP2XS

Allure DGPO 10A with Extra Switch

Technical properties

Configuration

Number of modules	2
-------------------	---

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Materials

Colour	white
Surface appearance	glossy

Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Number of socket outlets switchable	2
With transparent product label holder	No

Safety

IK protection code against mechanical impacts	IK08
REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection

Identification

Main design line	Allure
------------------	--------