



WBHP2XS

## Allure DGPO 10A with Extra Switch

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Connectivity

With USB charging socket	No
--------------------------	----

#### Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

#### Electric current

Rated current	10 A
---------------	------

#### Materials

Colour	white
--------	-------

#### Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Number of socket outlets switchable	2
With transparent product label holder	No

#### Safety

Protection index IP	IP2X
REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection