



WBHP2XS

Allure DGPO 10A with Extra Switch

Technical properties

Configuration

Number of modules 2

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

Electric current

Rated current 10 A

Materials

Colour white

Surface appearance glossy

Installation, mounting

Mounting type flush-mounted

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Equipment

Number of socket outlets switchable 2

With transparent product label holder No

Safety

IK protection code against mechanical impacts IK08

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

Identification

Main design line Allure