



WBHP2XS-MB

Allure DGPO 10A with Extra Switch MB

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Frequency	50 Hz
-----------	-------

Electric current

Rated current	10 A
---------------	------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Number of socket outlets switchable	2
-------------------------------------	---

Safety

RoHS conform	Yes
--------------	-----

Identification

Main design line	Allure
------------------	--------