



WBHP2XS-MW

Allure DGPO 10A with Extra Switch MW

Technical properties

Configuration

Number of modules 2

Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

Electric current

Rated current 10 A

Installation, mounting

Mounting type flush-mounted

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Equipment

Number of socket outlets switchable 2

Identification

Main design line Allure