



WBM10I

Mechanism 10A intermediate

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Configuration

Switch mode	intermediate
Antibacterial treatment	No

Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Electric current

Rated current	10 A
---------------	------

Materials

Colour	white
--------	-------

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Safety

REACH conform	Yes
RoHS conform	Yes