



WBM20

#### Technical properties

##### Architecture

Type of control unit	rocker
----------------------	--------

##### Main electrical features

Nominal voltage	250 V AC
-----------------	----------

##### Electric current

Rated current	20 A
---------------	------

##### Connection

Type of connection	with screw terminals
--------------------	----------------------

Type of connection	Screw connection
--------------------	------------------