




WBM32H-MB



## Mechanism 32A MB "HOB"

### Technical properties

#### Electric current

|               |      |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Materials

|        |       |
|--------|-------|
| Colour | Black |
|--------|-------|

|                |      |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

|           |           |
|-----------|-----------|
| Treatment | Varnished |
|-----------|-----------|

#### Identification

|                      |  |
|----------------------|--|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|--|

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Texts

|                   |          |
|-------------------|----------|
| Installation mode | RotoLoc® |
|-------------------|----------|

|                    |                      |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

|          |                        |
|----------|------------------------|
| Lighting | For monitoring circuit |
|----------|------------------------|

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|