



WBMCAT5

Mechanism cat5 data

Technical properties

Configuration

Category / ports	cat.5e
------------------	--------

Connectivity

Outlet	with straight outlet
--------	----------------------

Dimensions

Height	27 mm
Width	27 mm

Frequency

Transmission bandwidth	max. 100 MHz
------------------------	--------------

Resistance

Signal contact resistance	< 20 mΩ
Insulation resistance	min. 500 MΩ at 100 VDC

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...60 °C
Relative humidity (without condensation)	10...90 %