



WBP1XXS

## Technical properties

### Configuration

Number of modules	1
-------------------	---

### Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

### Electric current

Rated current	10 A
---------------	------

### Dimensions

Insertion depth	16 mm
Height	77 mm
Width	117 mm

### Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

### Connection

Type of connection	with screw terminals
--------------------	----------------------

### Equipment

Number of socket outlets switchable	1
-------------------------------------	---

### Safety

Protection index IP	IP20
---------------------	------