



WBP4S

**Premiere 10A DP horz 4 gang GPO**

**Technical properties**

**Configuration**

Number of modules	4
-------------------	---

**Main electrical features**

Nominal voltage	250 V AC
Frequency	50 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Insertion depth	0 mm
Height	78 mm
Width	211 mm

**Installation, mounting**

Mounting type	flush-mounted
Installation mode	for screw fastening

**Connection**

Type of connection	with screw terminals
--------------------	----------------------

**Scope of delivery**

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

**Equipment**

Number of socket outlets switchable	4
-------------------------------------	---

**Safety**

Protection index IP	IP20
---------------------	------