



WBQHSP2-MB

## FIN 2 Gang Hybrid MB

### Technical properties

#### Dimensions

Height	117 mm
Width	77 mm

#### Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

#### Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

#### Safety

RoHS conform	Yes
Halogen free	Yes

#### Identification

Main design line	Finesse
------------------	---------