



WBQP115S-MW

## FIN Single GPO 15A MW

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

#### Electric current

Rated current	15 A
---------------	------

#### Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

#### Equipment

Number of socket outlets switchable	1
-------------------------------------	---

#### Safety

REACH conform	Yes
RoHS conform	Yes