



WBQP1R-MW

FIN Single GPO 10A with round Earth MW

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Equipment

Number of socket outlets switchable	0
-------------------------------------	---

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes