



WBQP2S

FIN DGPO 10A

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Materials

Colour	white
Surface appearance	glossy

Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
--------------------	----------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	2
With transparent product label holder	No

Safety

IK protection code against mechanical impacts	IK08
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection

Identification

Main design line	Finesse
------------------	---------