



WBQP2S

FIN DGPO 10A

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V AC |
| Frequency | 50 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Materials

| | |
|--------------------|--------|
| Colour | white |
| Surface appearance | glossy |

Installation, mounting

| | |
|-------------------|------------------------|
| Entries | cable entries bevelled |
| Mounting type | flush-mounted |
| Installation mode | for screw fastening |

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

Scope of delivery

| | |
|-------------------|--|
| Scope of delivery | supplied with standard tapered point 32 mm fixing screws |
|-------------------|--|

Equipment

| | |
|---------------------------------------|----|
| Number of socket outlets switchable | 2 |
| With transparent product label holder | No |

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | IK08 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | Enhanced contact protection |

Identification

| | |
|------------------|---------|
| Main design line | Finesse |
|------------------|---------|