



WBQP2XS

## FIN DGPO 10A with Extra Switch

### Technical properties

#### Configuration

Number of modules 2

#### Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

#### Electric current

Rated current 10 A

#### Installation, mounting

Mounting type flush-mounted

Installation mode for screw fastening

#### Connection

Type of connection with screw terminals

#### Equipment

Number of socket outlets switchable 2

#### Safety

REACH conform Yes

RoHS conform Yes

#### Identification

Main design line Finesse