



WBQP2XS

## FIN DGPO 10A with Extra Switch

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Frequency	50 Hz
-----------	-------

#### Electric current

Rated current	10 A
---------------	------

#### Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Number of socket outlets switchable	2
-------------------------------------	---

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Identification

Main design line	Finesse
------------------	---------