



WBQP2XS-MW

FIN DGPO 10A with Extra Switch MW

Technical properties

Configuration

Number of modules	2
-------------------	---

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Materials

Colour	white
Surface appearance	matt

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Number of socket outlets switchable	2
With transparent product label holder	No

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	Enhanced contact protection