



WBSA2

2 Gang Architrave Switch

Technical properties

Architecture

Type of control unit rocker

Configuration

Switch mode 2 way, with loop terminal

Controls and indicators

Number of buttons 2

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC/DC

Frequency 50 Hz

Electric current

Rated current 16 AX

Dimensions

Height 85 mm

Width 36 mm

Materials

Colour white

Colour white

Surface appearance glossy

Installation, mounting

Mounting type flush-mounted

Installation mode for screw fastening

Connection

Terminal terminals accommodate 4 x 1.5 mm² cable

Type of connection with screw terminals

Type of connection Screw connection

Scope of delivery

Scope of delivery supplied with tapered point 12 mm fixing screws ;
supplied with both a premiere and a visage cover

Identification

Main design line visage/premiere