



WBSA3

Premiere 3G architrave switch

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Configuration

Switch mode	2 way, with loop terminal
-------------	---------------------------

Controls and indicators

Number of buttons	3
-------------------	---

Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	250 V AC/DC
---------------	-------------

Frequency	50 Hz
-----------	-------

Electric current

Rated current	16 AX
---------------	-------

Dimensions

Height	113 mm
--------	--------

Width	36 mm
-------	-------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

Connection

Terminal	terminals accommodate 4 x 1.5 mm ² cable
----------	---

Type of connection	with screw terminals
--------------------	----------------------

Type of connection	Screw connection
--------------------	------------------

Scope of delivery

Scope of delivery	supplied with tapered point 12 mm fixing screws
-------------------	---

Identification

Main design line	premiere
------------------	----------