




WBSCKSV1-MB



## Silhouette 40A 2 pole Cooker Switch MB

### Technical properties

#### Electric current

Rated current	40 A
---------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Materials

Colour	Black
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Built-in depth	22 mm
----------------	-------

#### Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

#### Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole off