




WBSP1S



Silhouette 10A socket Horz + shutter

Technical properties

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type | Screw mounting |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Dimensions

| | |
|----------------|--------|
| Built-in depth | 23 mm |
| Height | 77 mm |
| Width | 117 mm |
| Depth | 28 mm |

Materials

| | |
|----------------|--------------------|
| Colour | White |
| Surface finish | Glossy |
| Material | Polycarbonate (PC) |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Equipment

| | |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert | No |
| With hinged lid | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Texts

| | |
|---------|------------------|
| Imprint | Without imprint |
| Cover | Full cover plate |

| | |
|--------------------|-----------------------------|
| Protection | Enhanced contact protection |
| Type of connection | With screw terminals |
| Related Series | silhouette |