




WBSP1S-MW



Silhouette 10A socket Horz + shutter MW

Technical properties

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Built-in depth	23 mm
----------------	-------

Height	77 mm
--------	-------

Width	117 mm
-------	--------

Depth	28 mm
-------	-------

Materials

Colour	White
--------	-------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC)
----------	--------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
-----------------------------------	---------------------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals
Related Series	silhouette